

# STS060A-HT2 Cut Sheet



Metrol limit switch, high temperature, stopper bolt, 6mm diameter, threaded, 1mm pitch, 31.7mm length, 3.4mm flat head, stainless steel, 1.5mm plunger, 1N contact force, N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STS060A-HT2>

## Technical Specifications

Brand	Metrol
Item	Limit switch
Application	High temperature
Switch Type	Stopper bolt
Diameter	6mm
Barrel Type	Threaded
Length	31.7mm
Head Type	3.4mm flat
Actuator Type	1.5mm plunger
Contact Force	1N
Contact Type	N.O.
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	24 AWG
Stroke	0.7mm
Repeatability	0.01mm
Impact Resistance	0.4 joules
Withstand Load	5000N
Thread Pitch	1mm
Material	Stainless steel
IP Rating	IP65
Operating Temperature	0 to 80 deg C
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>