


# STXR600Y05N Cut Sheet



Mersen STXR series power Surge Protective Device (SPD), 20 kA discharge current, 600/347 VAC 3-Phase Wye, neutral ground protection, parallel circuit, NEMA 4/4X enclosure rating, 3/4in NPSM mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STXR600Y05N>

## Technical Specifications

<b>Brand</b>	Mersen
<b>Item</b>	Surge Protective Device (SPD)
<b>Series</b>	STXR
<b>Surge Protection Type</b>	Power protection
<b>UL Type</b>	UL Type 1
<b>Circuit Type</b>	Parallel circuit
<b>Neutral Ground Protection</b>	Yes
<b>System Voltage</b>	600/347 VAC 3-Phase Wye
<b>Nominal Discharge Current</b>	20 kA
<b>Voltage Protection Rating (VPR)</b>	2500V (L-L, L-G), 1500V (L-N), 1000V (N-G)
<b>Per Phase Max Surge Capacity</b>	50 kA
<b>Indicating Type</b>	LED indication
<b>SCCR Rating</b>	200kA SCCR
<b>UL Rating</b>	UL 1449 rated
<b>Enclosure Rating</b>	NEMA 4/4X
<b>Mounting</b>	3/4in NPSM
<b>Connection</b>	4-wire with ground 10 AWG pigtail
<b>Additional Information</b>	Optional wall/panel mounting bracket available

## Agency Approvals

<b>UL Listed File #</b>	E210793
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	162842
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>