

SV-1120-30-H Cut Sheet



CITO StackValve modular solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, stackable, Cv=8.5, 120 VAC operating voltage, 12VA, 18mm DIN style wiring plug. RA-3903 high-flow turbine and SF-9130 screen included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV-1120-30-H>

Technical Specifications

Brand	CITO
Item	Valve
Working Fluid	Coolant, oil or water
Valve Type	Solenoid process
Series	StackValve
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Glass-filled nylon
Stackable	Yes
Flow Coefficient	8.5

Maximum Operating Pressure	100 psi
Minimum Operating Pressure	5 psi
Working Fluid Temperature	20 to 160 deg F
Operating Voltage	120 VAC
Power Rating	12VA
Electrical Connection	18mm DIN style wiring plug
Indicating Type	LED indication
Form Factor	Modular
Includes	RA-3903 high-flow turbine and SF-9130 screen

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SV-1120-30-H.pdf>
See store item page for other formats.