

SVNK228 Cut Sheet



Quadritalia vertical enclosure barrier, adjustable position, galvanized steel. For use with 2200 x 800mm (H x D) OK series enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SVNK228>

Technical Specifications

Brand	Quadritalia
Item	Vertical enclosure barrier
Adjustable Position	Yes
Height	2093mm
Width	30.5mm
Depth	700mm
Material	Galvanized steel
For Use With	2200 x 800mm (H x D) OK series enclosures
Includes	Mounting hardware
Application	Vertically separates OK Series enclosures into two sections

Agency Approvals

UL Listed File #	None
UL Recognized File #	E503249
UL Hazardous File #	None
CE	View CE declarations
CSA File #	115232
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SVNK228.pdf>
See store item page for other formats.