

# T121224CHSS Cut Sheet



Wiegmann wiring trough, 12 x 12 x 24in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, No. 3 intermediate polished finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T121224CHSS>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Wiring trough
<b>NEMA Rating</b>	1/4/4X/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	12 x 24 x 12in (HxWxD)
<b>Enclosure Height</b>	12.22in
<b>Enclosure Depth</b>	12.25in
<b>Enclosure Length</b>	24.31in

<b>Integral Mounting Feet</b>	Yes
<b>Knockouts</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	No. 3 intermediate polished
<b>Cover Type</b>	Single-door
<b>Latch Type</b>	Stainless steel clamps
<b>Padlockable</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E32576
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T121224CHSS.pdf>  
See store item page for other formats.