

# T121248CH Cut Sheet



Wiegmann wiring trough, 12 x 12 x 48in (HxDxL), NEMA 4, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T121248CH>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Wiring trough
<b>NEMA Rating</b>	4
<b>Nominal Enclosure Dimensions</b>	12 x 48 x 12in (HxWxD)
<b>Enclosure Height</b>	12.22in
<b>Enclosure Depth</b>	12.25in
<b>Enclosure Length</b>	48.31in

<b>Integral Mounting Feet</b>	Yes
<b>Knockouts</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door
<b>Latch Type</b>	Plated steel clamps

## Agency Approvals

<b>UL Listed File #</b>	E32576
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	None
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T121248CH.pdf>  
See store item page for other formats.