

T201612HWT Cut Sheet



AttaBox Triton series enclosure, NEMA 1/3/3R/4X/12, 20 x 16 x 12in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T201612HWT>

Technical Specifications

Brand	AttaBox	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Triton	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Fiberglass reinforced polyester
Slope Top	No	Color	Gray
NEMA Rating	1/3/3R/4X/12	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Height	20in	Number of Hinges Per Door	1
Nominal Enclosure Width	16in	Latch Type	(2) twist-lock latches
Nominal Enclosure Depth	12in	Padlock Attachment Type	Padlock hasp and staple
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T201612HWT.pdf>
See store item page for other formats.