

T2212CHSS Cut Sheet



Wiegmann wiring trough, 2.5 x 2.5 x 12in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, No. 3 intermediate polished finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2212CHSS>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Wiegmann |
| Item | Wiring trough |
| NEMA Rating | 1/4/4X/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 3 x 12 x 3in (HxWxD) |
| Enclosure Height | 2.72in |
| Enclosure Depth | 2.75in |
| Enclosure Length | 12.31in |

| | |
|-------------------------------|-----------------------------|
| Integral Mounting Feet | Yes |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Single-door |
| Latch Type | Stainless steel clamps |
| Padlockable | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E32576 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T2212CHSS.pdf>
See store item page for other formats.