


T30060-3CR Cut Sheet



Bussmann fuse block, accepts T fuses, 60A, 300V, 3-pole, 14-2 AWG copper or aluminum, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30060-3CR>

Technical Specifications

| | |
|----------------------------------|-----------------------------|
| Brand | Bussmann |
| Item | Fuse block |
| Modular | No |
| Blown Fuse Indicator | No |
| Multi-Wire | No |
| Accepts Fuse Class | T |
| Amperage Rating | 60A |
| Voltage Rating | 300V |
| Number of Poles | 3 |
| Conductor Size | 14-2 AWG copper or aluminum |
| Conductor Connection Type | Box lug |
| SCCR Rating | 200kA SCCR |
| Fuse Connection Type | Clip with reinforced spring |
| Mounting | Panel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E14853 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 47235 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |