

T363012HWTSL Cut Sheet



AttaBox Triton series enclosure, NEMA 1/3/3R/4X/12, 36 x 30 x 12in (HxWxD), fiberglass reinforced polyester, Pantone 428 C glacier gray, single-door, 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T363012HWTSL>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	Triton
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3/3R/4X/12
IP Rating	IP66
Nominal Enclosure Height	36in
Nominal Enclosure Width	30in
Nominal Enclosure Depth	12in
Integral Mounting Feet	Yes

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Pantone 428 C glacier gray
Cover Type	Single-door
Latch Type	1/4-turn flush-mounted latch
Number Of Latches	1
Secondary Latch Type	Twist-lock latch
Number Of Secondary Latches	4
Padlockable	Yes

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T363012HWTSL.pdf>
See store item page for other formats.