

TA0521S0403 Cut Sheet

CCEA TRACKALPHA series LED light bar, 681mm length, 24 VDC operating voltage, daylight white, 5000K, 32.5W, bracket mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA0521S0403>



Technical Specifications

| | |
|--------------------------|-------------------|
| Brand | CCEA |
| Item | LED light bar |
| Series | TRACKALPHA |
| Length | 681mm |
| Operating Voltage | 24 VDC |
| LED Color | Daylight white |
| Color Temperature | 5000K |
| Mounting | Bracket |
| Connection | Pigtail |
| Power Consumption | 32.5W |
| Body Material | Anodized aluminum |
| Cable Length | 9.8ft/3m |
| IP Rating | IP67 |
| Includes | Mounting bracket |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E506617 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TA0521S0403.pdf>
See store item page for other formats.