

TA0521S04W03 Cut Sheet



CCEA TRACKALPHA-PRO series LED light bar, 681mm length, 24 VDC operating voltage, daylight white, 5000K, 32.5W, 3250 lm, bracket mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67 and IP69. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TA0521S04W03>

Technical Specifications

Brand	CCEA
Item	LED light bar
Series	TRACKALPHA-PRO
Length	681mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	5000K
Luminous Flux	3250 lm

Mounting	Bracket
Connection	Pigtail
Power Consumption	32.5W
Body Material	Anodized aluminum
Cable Length	9.8ft/3m
IP Rating	IP67 and IP69
Includes	Mounting bracket

Agency Approvals

UL Listed File #	NONE
UL Recognized File #	E506617
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TA0521S04W03.pdf>
See store item page for other formats.