

TKM-15-P Cut Sheet



ICON Process Controls TruFlo flow meter, paddle wheel, 1/2in schedule 80 PVC socket process connection, 1 to 32 GPM, 0 to 999,999 gallons, Output 1: switch, Output 2: switch or pulse, Output 3: analog.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TKM-15-P>

Technical Specifications

Brand	ICON Process Controls	Measuring Range 2	0 to 999,999 gallons
Item	Flow meter	Volume Flow Totalizer Units	Gal, l, kl, selectable
Series	TruFlo	Output	Switch (N.O./N.C.), NPN selectable
Media Type	Liquid	Output 2	Switch (N.O./N.C.) or pulse, NPN selectable
Sensing Type	Paddle wheel	Output 3	Analog, 4-20 mA
Process Connection	1/2in schedule 80 PVC socket	Operating Voltage	9-30 VDC
Measuring Range	1 to 32 GPM	Electrical Connection	8-pin M12 quick-disconnect
Volume Flow Rate Units	GPM, l/min, selectable	Includes	(1) 9.8ft/3m power cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TKM-15-P.pdf>
See store item page for other formats.