

TKM-20-P Cut Sheet



ICON Process Controls TruFlo flow meter, paddle wheel, 3/4in schedule 80 PVC socket process connection, 1.5 to 45 GPM, 0 to 999,999 gallons, Output 1: switch, Output 2: switch or pulse, Output 3: analog.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TKM-20-P>

Technical Specifications

Brand	ICON Process Controls
Item	Flow meter
Series	TruFlo
Media Type	Liquid
Sensing Type	Paddle wheel
Process Connection	3/4in schedule 80 PVC socket
Measuring Range	1.5 to 45 GPM
Volume Flow Rate Units	GPM, l/min, selectable

Measuring Range 2	0 to 999,999 gallons
Volume Flow Totalizer Units	Gal, l, kl, selectable
Output	Switch (N.O./N.C.), NPN selectable
Output 2	Switch (N.O./N.C.) or pulse, NPN selectable
Output 3	Analog, 4-20 mA
Operating Voltage	9-30 VDC
Electrical Connection	8-pin M12 quick-disconnect
Includes	(1) 9.8ft/3m power cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TKM-20-P.pdf>
See store item page for other formats.