

# TKM-50-P Cut Sheet



ICON Process Controls TruFlo flow meter, paddle wheel, 2in schedule 80 PVC socket process connection, 10.5 to 357 GPM, 0 to 999,999 gallons, Output 1: switch, Output 2: switch or pulse, Output 3: analog.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TKM-50-P>

## Technical Specifications

Brand	ICON Process Controls
Item	Flow meter
Series	TruFlo
Media Type	Liquid
Sensing Type	Paddle wheel
Process Connection	2in schedule 80 PVC socket
Measuring Range	10.5 to 357 GPM
Volume Flow Rate Units	GPM, l/min, selectable

Measuring Range 2	0 to 999,999 gallons
Volume Flow Totalizer Units	Gal, l, kl, selectable
Output	Switch (N.O./N.C.), NPN selectable
Output 2	Switch (N.O./N.C.) or pulse, NPN selectable
Output 3	Analog, 4-20 mA
Operating Voltage	9-30 VDC
Electrical Connection	8-pin M12 quick-disconnect
Includes	(1) 9.8ft/3m power cable

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/TKM-50-P.pdf>  
See store item page for other formats.