


TRM-10-D-120AD Cut Sheet



ProSense multi-mode relay timer, 0.05 seconds to 999 hours selectable timing range, 120 VAC/VDC operating voltage, 10A contact rating, (1) DPDT timed relay output(s), socket mount, 11-pin. Requires Macromatic 70170-D relay socket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRM-10-D-120AD>

Technical Specifications

Brand	ProSense
Item	Relay timer
Timer Type	Multi-mode
Indicator	LED
Timing Range	0.05 seconds to 999 hours selectable
Operating Voltage	120 VAC/VDC
Timer Output Type(s)	(1) DPDT timed relay
Timer Function(s)	<ul style="list-style-type: none">• on-delay• triggered on-delay• off-delay• on/off delay• interval• single-shot• falling edge (single-shot)• on-flasher• off-flasher• watchdog
Contact Rating	10A
Mounting	Socket
Connector Type	11-pin
Requires	Macromatic 70170-D relay socket

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	602618
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document