

# TRM-16-D-24AD Cut Sheet



ProSense multi-mode relay timer, 0.05 seconds to 10,230 hours selectable timing range, 24 VAC/VDC operating voltage, 10A contact rating, (1) DPDT timed relay output(s), socket mount, 11-pin. Requires Macromatic 70170-D relay socket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRM-16-D-24AD>

## Technical Specifications

|                             |   |
|-----------------------------|---|
| <b>Brand</b>                | ProSense  |
| <b>Item</b>                 | Relay timer   |
| <b>Timer Type</b>           | Multi-mode  |
| <b>Indicator</b>            | LED   |
| <b>Timing Range</b>         | 0.05 seconds to 10,230 hours selectable   |
| <b>Operating Voltage</b>    | 24 VAC/VDC  |
| <b>Timer Output Type(s)</b> | (1) DPDT timed relay  |
| <b>Timer Function(s)</b>    | <ul style="list-style-type: none"><li>• on-delay</li><li>• triggered on-delay</li><li>• off-delay</li><li>• on/off delay</li><li>• on-interval</li><li>• flasher (single-shot)</li><li>• on-flasher</li><li>• on-delay/flasher</li><li>• off-flasher</li><li>• watchdog</li><li>• single-shot</li><li>• falling edge (single-shot)</li><li>• on-cycle</li><li>• off-cycle</li><li>• delayed interval</li><li>• triggered delayed interval</li></ul> |
| <b>Contact Rating</b>       | 10A   |
| <b>Mounting</b>             | Socket  |
| <b>Connector Type</b>       | 11-pin  |
| <b>Requires</b>             | Macromatic 70170-D relay socket   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E191059                                |
| <b>UL Recognized File #</b> | E191059                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 602618                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |