

UH5947-04-001PC24 Cut Sheet



Dold safety relay, motor standstill, speed and safety gate monitoring, multi delay functions, (2) NAMUR sensor inputs and/or (1) encoder, 2-channel, 24 VDC, (4) N.O. safety output(s), (2) status monitoring output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UH5947-04-001PC24>

Technical Specifications

Brand	Dold
Item	Safety relay
Relay Type	Motor standstill, speed and safety gate monitoring
Delay Type	Multi delay functions
Monitoring Circuit	(2) NAMUR sensor inputs and/or (1) encoder
Number Of Channels	2
Control Voltage	24 VDC
Restart Type	Manual or automatic restart
Safety Output Type	(4) N.O.
Monitoring Output Type	(2) status
Connection	Push-in cage clamp

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/UH5947-04-001PC24.pdf>
See store item page for other formats.