

# ULPCM125125G Cut Sheet



Fibox MNX series enclosure, NEMA 1/4/4X/6, 130 x 130 x 125 mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ULPCM125125G>

## Technical Specifications

<b>Brand</b>	Fibox
<b>Item</b>	Enclosure
<b>Series</b>	MNX
<b>Subpanel</b>	Purchase subpanel separately
<b>NEMA Rating</b>	1/4/4X/6
<b>IP Rating</b>	IP67
<b>Enclosure Height</b>	130.00 mm

<b>Enclosure Width</b>	130.00 mm
<b>Enclosure Depth</b>	127.00 mm
<b>Cover Type</b>	Screw cover
<b>Cover Depth</b>	77 mm
<b>Integral Mounting Flange</b>	No
<b>Material</b>	Polycarbonate
<b>Color</b>	RAL 7035 light gray

## Agency Approvals

<b>UL Listed File #</b>	E75645
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/ULPCM125125G.pdf>  
See store item page for other formats.