

ULTPCM131308 Cut Sheet



Fibox TEMPO series enclosure, NEMA 1/4/4X, 130 x 130 x 75 mm (HxWxD), polycarbonate, RAL 7035 light gray, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ULTPCM131308>

Technical Specifications

Brand	Fibox
Item	Enclosure
Series	TEMPO
NEMA Rating	1/4/4X
IP Rating	IP65
Enclosure Height	130.00 mm
Enclosure Width	130.00 mm
Enclosure Depth	75.00 mm
Cover Type	Hinged screw cover
Cover Depth	13 mm
Integral Mounting Flange	No
Material	Polycarbonate
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E75645
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ULTPCM131308.pdf>
See store item page for other formats.