

# US06-0001-00 Cut Sheet



Flowline EchoTouch intrinsically safe reflective ultrasonic liquid level sensor, 19.6ft/6m sensing range, 4-20 mA, 14-28 VDC operating voltage, LCD digital display with pushbuttons, 2in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/US06-0001-00>

## Technical Specifications

<b>Brand</b>	Flowline	<b>IP Rating</b>	IP66
<b>Item</b>	Level sensor	<b>NEMA Rating</b>	4X
<b>Series</b>	EchoTouch	<b>Process Connection</b>	2in male NPT
<b>Sensor Type</b>	Intrinsically safe reflective ultrasonic	<b>Electrical Connection</b>	Screwless terminals, 1/2in female NPT
<b>Media Type</b>	Liquid	<b>Display Type</b>	LCD digital display with pushbuttons
<b>Mounting</b>	Vertical top	<b>Includes</b>	LM90-1001 cable gland with 1/2in male NPT thread
<b>Process Temperature</b>	-40 to 176 deg F	<b>Requires</b>	An LI99-2001 Fob USB adapter (purchased separately) and WEBCAL software (free download from the AutomationDirect Web site) are required for full sensor configuration and firmware updates. Limited configuration is available via the pushbuttons and display.
<b>Sensing Range</b>	19.6ft/6m	<b>Application</b>	Hazardous location rated
<b>Output</b>	4-20 mA		
<b>Operating Voltage</b>	14-28 VDC		
<b>Housing Size</b>	3.42in diameter (25 deg tilt)		
<b>Housing Material</b>	Aluminum		

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	178551
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">CSA Control Drawing</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/US06-0001-00.pdf>  
See store item page for other formats.