

# VCT-50-1000 Cut Sheet



ProSense vibration transmitter, 0 to 50 mm/s RMS, 10-1000 Hz, 4-20 mA output, 1/4-28 UNF female process connection, 4-pin M12 quick-disconnect, 9.6 to 32 VDC operating voltage, IP67 IP68 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VCT-50-1000>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Vibration transmitter
<b>Measuring Range</b>	0 to 50 mm/s RMS
<b>Frequency Range</b>	10-1000 Hz
<b>Output</b>	4-20 mA
<b>Process Connection</b>	1/4-28 UNF female
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Operating Temperature</b>	-30 to 125 deg C
<b>Operating Voltage</b>	9.6 to 32 VDC
<b>IP Rating</b>	IP67 IP68 IP69K
<b>Includes</b>	(1) 1/4-28 UNF male to M8 x 1.25mm male process adapter and (1) 1/4-28 UNF male to 1/4-28 UNF male process adapter
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E197592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>