

# VE0521S01 Cut Sheet

CCEA VEGA series LED light bar, 706mm length, 24 VDC operating voltage, daylight white, 5000K, 32.5W, recessed mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67 and IP69.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VE0521S01>

## Technical Specifications

<b>Brand</b>	CCEA
<b>Item</b>	LED light bar
<b>Series</b>	VEGA
<b>Length</b>	706mm
<b>Operating Voltage</b>	24 VDC
<b>LED Color</b>	Daylight white
<b>Color Temperature</b>	5000K
<b>Mounting</b>	Recessed
<b>Connection</b>	Pigtail
<b>Power Consumption</b>	32.5W
<b>Body Material</b>	Anodized aluminum
<b>Cable Length</b>	9.8ft/3m
<b>IP Rating</b>	IP67 and IP69

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E506617
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/VE0521S01.pdf>  
See store item page for other formats.