

VFL75-100L-3H Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 3.44in insertion length, 316L stainless steel wetted parts, -40 to 212 deg F, 3/4in male NPT process connection, switch PNP, 3-wire, N.O./N.C. complementary, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-100L-3H>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Vibration fork
Media Type	Liquid
Mounting	Any orientation
Insertion Length	3.44in
Process Connection	3/4in male NPT
Process Temperature	-40 to 212 deg F
Output	Switch PNP, 3-wire, N.O./N.C. complementary
Operating Voltage	10-30 VDC
Wetted Parts	316L stainless steel
Electrical Connection	4-pin M12 quick-disconnect

Agency Approvals

CE	View CE declarations
CSA File #	600062
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document