

VFL75-100S-3D Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 1.89in insertion length, 316L stainless steel wetted parts, -40 to 212 deg F, 3/4in male NPT process connection, switch PNP, 3-wire, N.O. or N.C., EN 175301-803-A connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-100S-3D>

Technical Specifications

| | |
|------------------------------|----------------------------------|
| Brand | ProSense |
| Item | Level switch |
| Sensor Type | Vibration fork |
| Media Type | Liquid |
| Mounting | Any orientation |
| Insertion Length | 1.89in |
| Process Connection | 3/4in male NPT |
| Process Temperature | -40 to 212 deg F |
| Output | Switch PNP, 3-wire, N.O. or N.C. |
| Operating Voltage | 10-30 VDC |
| Wetted Parts | 316L stainless steel |
| Electrical Connection | EN 175301-803-A connector |

Agency Approvals

| | |
|--------------------|--|
| CE | View CE declarations |
| CSA File # | 600062 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |