

VRTP-125-IR-A12 Cut Sheet



Elesa handwheel, spoked, 125mm diameter, 12mm bore, foldaway revolving handle, polypropylene, matte black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VRTP-125-IR-A12>

Technical Specifications

| | |
|-------------------------|---------------------------|
| Brand | Elesa |
| Item | Handwheel |
| Wheel Type | Spoked |
| Nominal Diameter | 125mm |
| Bore Diameter | 12mm |
| Handle Type | Foldaway revolving handle |
| Material | Polypropylene |
| Color | Matte black |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VRTP-125-IR-A12.pdf>
See store item page for other formats.