

W1C42 Cut Sheet



Wiegmann operator console, NEMA 12/13, 40 x 42 x 20in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/W1C42>

Technical Specifications

Brand	Wiegmann
Item	Operator console
Subpanel	Subpanel included
NEMA Rating	12/13
Nominal Enclosure Dimensions	40 x 42 x 20in (HxWxD)
Enclosure Height	40.41in
Enclosure Width	42.00in
Enclosure Depth	21.03in
Mounting	Freestanding
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Double-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point keylocking handle
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document