

WA722418FSN43PT Cut Sheet



Wiegmann enclosure, NEMA 3/4/12, 72 x 24 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA722418FSN43PT>

Technical Specifications

Brand	Wiegmann	Knockouts	No
Item	Enclosure	Material	Carbon steel
Subpanel	Purchase subpanel separately	Color	ANSI 61 gray
Slope Top	No	Finish	Powder coat
NEMA Rating	3/4/12	Cover Type	Single-door
Nominal Enclosure Height	72in	Hinge Type	Continuous hinge
Nominal Enclosure Width	24in	Number of Hinges Per Door	1
Nominal Enclosure Depth	18in	Latch Type	3-point keylocking/padlocking combo handle
Mounting	Freestanding	Padlockable	Yes
Dual Access	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA722418FSN43PT.pdf>
See store item page for other formats.