

# WA72CPX7318U Cut Sheet



Wiegmann disconnect enclosure, NEMA 12, center post, 72 x 73 x 18in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA72CPX7318U>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Wiegmann             |
| <b>Item</b>                     | Disconnect enclosure |
| <b>Slope Top</b>                | No                   |
| <b>NEMA Rating</b>              | 12                   |
| <b>Disconnect Mounting</b>      | Center post          |
| <b>Nominal Enclosure Height</b> | 72.13in              |
| <b>Nominal Enclosure Width</b>  | 73.75in              |
| <b>Nominal Enclosure Depth</b>  | 19.36in              |
| <b>Mounting</b>                 | Floor                |
| <b>Material</b>                 | Carbon steel         |
| <b>Color</b>                    | ANSI 61 gray         |
| <b>Finish</b>                   | Powder coat          |

|                                  |                                                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------|
| <b>Cover Type</b>                | 2-door                                                                                                            |
| <b>Hinge Type</b>                | Continuous hinge                                                                                                  |
| <b>Number of Hinges Per Door</b> | 1                                                                                                                 |
| <b>Latch Type</b>                | 3-point padlocking handle                                                                                         |
| <b>Padlockable</b>               | Yes                                                                                                               |
| <b>Keylocking</b>                | No                                                                                                                |
| <b>Subpanel</b>                  | Purchase subpanel separately                                                                                      |
| <b>Requires</b>                  | Operator adapter plate (sold separately)                                                                          |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WA72CPX7318U.pdf>  
See store item page for other formats.