

# WA84XM3924SSN4 Cut Sheet



Wiegmann disconnect enclosure, NEMA 3R/4/4X/12, right flange, 84 x 39 x 24in (HxWxD), freestanding, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA84XM3924SSN4>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Wiegmann             |
| <b>Item</b>                     | Disconnect enclosure |
| <b>Slope Top</b>                | No                   |
| <b>NEMA Rating</b>              | 3R/4/4X/12           |
| <b>Disconnect Mounting</b>      | Right flange         |
| <b>Nominal Enclosure Height</b> | 84.12in              |
| <b>Nominal Enclosure Width</b>  | 39.5in               |
| <b>Nominal Enclosure Depth</b>  | 25.35in              |
| <b>Mounting</b>                 | Freestanding         |
| <b>Material</b>                 | 304 stainless steel  |

|                                  |                                                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------|
| <b>Finish</b>                    | No. 3 intermediate polished                                                                                       |
| <b>Cover Type</b>                | Single-door                                                                                                       |
| <b>Hinge Type</b>                | Stainless steel continuous hinge                                                                                  |
| <b>Number of Hinges Per Door</b> | 1                                                                                                                 |
| <b>Latch Type</b>                | 3-point padlocking handle                                                                                         |
| <b>Subpanel</b>                  | Subpanel included                                                                                                 |
| <b>Requires</b>                  | Operator adapter plate (sold separately)                                                                          |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WA84XM3924SSN4.pdf>  
See store item page for other formats.