

WA90XM3920U Cut Sheet



Wiegmann disconnect enclosure, NEMA 12, right flange, 90 x 39 x 20in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA90XM3920U>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	90 x 39 x 20in (HxWxD)
Enclosure Height	90.13in
Enclosure Width	39.50in
Enclosure Depth	21.29in
Mounting	Freestanding
Integral Mounting Feet	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included
Requires	Operator adapter plate (sold separately)

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA90XM3920U.pdf>
See store item page for other formats.