

WA90XM7718SSN4 Cut Sheet



Wiegmann disconnect enclosure, NEMA 3R/4/4X/12, right flange, 90 x 77 x 18in (HxWxD), freestanding, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA90XM7718SSN4>

Technical Specifications

Brand	Wiegmann	Finish	No. 3 intermediate polished
Item	Disconnect enclosure	Cover Type	2-door
Slope Top	No	Hinge Type	Stainless steel continuous hinge
NEMA Rating	3R/4/4X/12	Number of Hinges Per Door	1
Disconnect Mounting	Right flange	Latch Type	3-point padlocking handle
Nominal Enclosure Height	90.13in	Subpanel	Subpanel included
Nominal Enclosure Width	78.5in	Requires	Operator adapter plate (sold separately)
Nominal Enclosure Depth	19.35in	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Mounting	Freestanding		
Material	304 stainless steel		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA90XM7718SSN4.pdf>
See store item page for other formats.