

WA90XM7724SSN4 Cut Sheet



Wiegmann disconnect enclosure, NEMA 3R/4/4X/12, right flange, 90 x 77 x 24in (HxWxD), freestanding, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA90XM7724SSN4>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	3R/4/4X/12
Disconnect Mounting	Right flange
Nominal Enclosure Height	90.13in
Nominal Enclosure Width	78.5in
Nominal Enclosure Depth	25.35in
Mounting	Freestanding
Material	304 stainless steel

Finish	No. 3 intermediate polished
Cover Type	2-door
Hinge Type	Stainless steel continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point padlocking handle
Subpanel	Subpanel included
Requires	Operator adapter plate (sold separately)
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA90XM7724SSN4.pdf>
See store item page for other formats.