

WADW131602SS Cut Sheet



Wiegmann universal deep-hinged door, NEMA 3R/4/4X/12, 12.75 x 15.88 x 2.75in, 304 stainless steel, concealed hinges, polycarbonate window. For use with Hubbell-Wiegmann NEMA 3R, 4, 4X, or 12 rated enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WADW131602SS>

Technical Specifications

Brand	Wiegmann
Item	Universal deep-hinged door
NEMA Rating	3R/4/4X/12
Door Size	12.75 x 15.88 x 2.75in
Door Material	304 stainless steel
Hinge Type	Concealed hinges
Finish	No. 3 intermediate polished
Cutout Size	9.75 x 12.88in

Number of Hinges Per Door	1
Latch Type	1/4-turn semi-flush oil-tight latch
Gasket Type	Poured in place
Window Material	Polycarbonate
Window Size	8.63 x 9.83in
For Use With	Hubbell-Wiegmann NEMA 3R, 4, 4X, or 12 rated enclosures

Agency Approvals

UL Listed File #	None
UL Recognized File #	E64791
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WADW131602SS.pdf>
See store item page for other formats.