

# WC1224B Cut Sheet



Wiegmann operator console, NEMA 12/13, 36 x 24 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, flush single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC1224B>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Operator console
<b>Subpanel</b>	Subpanel included
<b>NEMA Rating</b>	12/13
<b>Nominal Enclosure Dimensions</b>	36 x 24 x 24in (HxWxD)
<b>Enclosure Height</b>	36.13in
<b>Enclosure Width</b>	24.13in
<b>Enclosure Depth</b>	24.06in
<b>Mounting</b>	Freestanding
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Flush single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	3-point keylocking handle
<b>Padlockable</b>	No
<b>Keylocking</b>	Yes
<b>Additional Information</b>	Purchase optional console top, writing desk and/or caster kit separately

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>