

WPBA1 Cut Sheet



Wiegmann pushbutton console, 1 hole, 30mm, NEMA 12/13, 4 x 3 x 5in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WPBA1>

Technical Specifications

| | |
|-------------------------------------|---------------------|
| Brand | Wiegmann |
| Item | Pushbutton console |
| Number of Pushbutton Holes | 1 hole |
| Pushbutton Hole Nominal Size | 30mm |
| Slope Top | No |
| NEMA Rating | 12/13 |
| Nominal Enclosure Dimensions | 4 x 3 x 5in (HxWxD) |
| Enclosure Height | 3.77in |
| Enclosure Width | 3.59in |
| Enclosure Depth | 4.88in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |