

WRD723624FS4 Cut Sheet



Wiegmann KwikHinge series enclosure, NEMA 3R/4/12, 72 x 36 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD723624FS4>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	No
Series	KwikHinge	Material	Carbon steel
Subpanel	Purchase subpanel separately	Color	ANSI 61 gray
Slope Top	No	Finish	Powder coat
NEMA Rating	3R/4/12	Cover Type	Single-door
IP Rating	IP66	Hinge Type	KwikHinge sliding hinge pins
Nominal Enclosure Height	72in	Number of Hinges Per Door	4
Nominal Enclosure Width	36in	Latch Type	3-point keylocking/padlocking combo handle
Nominal Enclosure Depth	24in	Padlockable	Yes
Mounting	Freestanding	Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD723624FS4.pdf>
See store item page for other formats.