

WRD723624SSFSN4 Cut Sheet



Wiegmann KwikHinge series enclosure, NEMA 3R/4/4X/12, 72 x 36 x 24in (HxWxD), freestanding mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD723624SSFSN4>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	No
Series	KwikHinge	Bottom Gland Plate	No
Subpanel	Purchase subpanel separately	Material	304 stainless steel
Slope Top	No	Finish	No. 3 intermediate polished
NEMA Rating	3R/4/4X/12	Cover Type	Single-door
IP Rating	IP66	Hinge Type	KwikHinge sliding hinge pins
Nominal Enclosure Height	72in	Number of Hinges Per Door	4
Nominal Enclosure Width	36in	Latch Type	3-point keylocking/padlocking combo handle
Nominal Enclosure Depth	24in	Number Of Latches	1
Mounting	Freestanding	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD723624SSFSN4.pdf>
See store item page for other formats.