

WRD902420FS4 Cut Sheet



Wiegmann KwikHinge series enclosure, NEMA 3R/4/12, 90 x 24 x 20in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD902420FS4>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Series | KwikHinge |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 3R/4/12 |
| IP Rating | IP66 |
| Nominal Enclosure Height | 90in |
| Nominal Enclosure Width | 24in |
| Nominal Enclosure Depth | 20in |
| Mounting | Freestanding |

| | |
|----------------------------------|--|
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | KwikHinge sliding hinge pins |
| Number of Hinges Per Door | 5 |
| Latch Type | 3-point keylocking/padlocking combo handle |
| Padlockable | Yes |
| Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD902420FS4.pdf>
See store item page for other formats.