

XCS-0B13-OD Cut Sheet



Killark control station cover assembly, hazardous location rated, single pilot light, single pushbutton, green, 110 VAC/VDC LED, red, momentary, (1) N.O. contact(s), blank legend plate(s), legend plate marking "START".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XCS-0B13-OD>

Technical Specifications

Brand	Killark
Item	Control station cover assembly
Application	Hazardous location rated
Factory Sealed	No
Housing Material	Aluminum
Control Station Configuration	Single pilot light, single pushbutton
Operator Color	Green
Indicator	110 VAC/VDC LED

Light Color(s)	Red
Action	Momentary
Contact Type	(1) N.O.
Legend Plate Type	Blank
Legend Plate Marking	START
NEMA Rating	7/9
Requires	SWB series splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XCS-0B13-OD.pdf>
See store item page for other formats.