

XEL-BSSCT Cut Sheet



LS Electric XGB bus coupler, 24 VDC, (2) Ethernet (RJ45) and (1) USB B port(s), EtherCAT Slave, 100 Mbps. For use with LS Electric XGB series I/O modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XEL-BSSCT>

Technical Specifications

Brand	LS Electric XGB
Item	Bus coupler
Voltage Rating	24 VDC
Number of Ports	2
Communication Port and Connection Type(s)	(2) Ethernet (RJ45) and (1) USB B port(s)
Port Protocol(s)	EtherCAT Slave
Port Speed(s)	100 Mbps

Number of Discrete Inputs/Outputs	256 inputs/256 outputs
Number of Analog Inputs/Outputs	64 inputs/32 outputs
Maximum Number of Data Bytes	512 input bytes/512 output bytes
For Use With	LS Electric XGB series I/O modules
Programming Software	XG5000 programming software v4.7 or later

Agency Approvals

UL Listed File #	E124950
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/XEL-BSSCT.pdf>
See store item page for other formats.