


XTOE1P6CGSS Cut Sheet



Eaton XT series electronic overload relay, 0.33-1.65A adjustable, solid state, ground fault protection, stand-alone power connection(s), DIN rail or panel mount. For use with any contactor.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/XTOE1P6CGSS>

Technical Specifications

| | |
|--------------------------|-----------------------|
| Brand | Eaton |
| Item | Relay |
| Series | XT |
| Relay Type | Electronic overload |
| Full Load Amperage Range | 0.33-1.65A adjustable |
| Operation Type | Solid state |
| Auxiliary Contacts | (1) N.O. / (1) N.C. |
| Trip Class | Selectable 10/20 |

| | |
|-------------------------|---|
| Phase Loss Sensitive | Yes |
| Ground Fault Protection | Yes |
| Connection | Stand-alone power |
| Mounting | DIN rail or panel |
| For Use With | Any contactor |
| Additional Information | Self powered, selectable phase imbalance and ground fault protection, optional communications available |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E1230 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 156828, 000353_0_000 |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/XTOE1P6CGSS.pdf>
See store item page for other formats.