

YN01-06505WL2000ST Cut Sheet



Sifam Tinsley B4 DC current shunt, 0–20 A, M5 terminal stud input connection, M4 screw output connection, 0–50 mV output, panel or DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/YN01-06505WL2000ST>

Technical Specifications

Brand	Sifam Tinsley
Series	B4
Item	DC current shunt
DC Current Range	0–20 A
Input Connection	M5 terminal stud
Output Connection	M4 screw
Output Voltage Range	0–50 mV
Accuracy	±0.5%
Mounting	Panel or DIN rail
Includes	Insulating base and polycarbonate cover

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/YN01-06505WL2000ST.pdf>
See store item page for other formats.