


ZP-S1-6FR-0P3M Cut Sheet



ZIPport bulkhead connector, 7/8in 6-pin female to pigtail, 16 AWG, 0.9ft/0.3m cable length, ether-based polyurethane conductor insulation material, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-S1-6FR-0P3M>

Technical Specifications

| | |
|-------------------------------|---|
| Brand | ZIPport |
| Item | Connector |
| Form Factor | Bulkhead |
| Connection 1 | 7/8in female with male threads 6-wire/6-pin |
| Connection 2 | Pigtail |
| Shielded | No |
| Cable Length | 0.9ft/0.3m |
| Conductor Size | 16 AWG |
| Conductor Insulation Material | Ether-based polyurethane |
| Housing Material | Anodized aluminum |
| IP Rating | IP67 |
| Includes | Mounting nut(s) |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E328610 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ZP-S1-6FR-0P3M.pdf>
See store item page for other formats.