


ZP-S1C-4FR-0P3M-18 Cut Sheet



ZPport bulkhead connector, 7/8in - 16 UN2 thread nut 4-pin female to pigtail, 18 AWG, 0.9ft/0.3m cable length, PVC conductor insulation material, European (Cenelec) color code. Mounting nut(s) included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZP-S1C-4FR-0P3M-18>

Technical Specifications

Brand	ZIPport
Item	Bulkhead connector
Connector Types	7/8in - 16 UN2 thread nut 4-pin female to pigtail
Conductor Size	18 AWG
Cable Length	0.9ft/0.3m
Conductor Insulation Material	PVC
Conductor Color Code	European (Cenelec)
Includes	Mounting nut(s)

Agency Approvals

UL Listed File #	E328610
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document