

ZV10H-235-02Z Cut Sheet



Schmersal IEC limit switch, side rotary adjustable 6mm plastic rod, 90-degree adjustable head, (2) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, M20 x 1.5 entry with 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ZV10H-235-02Z>

Technical Specifications

| | |
|------------------------------|--|
| Brand | Schmersal |
| Item | Limit switch |
| Switch Type | IEC |
| Actuator Type | Side rotary adjustable 6mm plastic rod |
| Head Type | 90-degree adjustable |
| Contact Type | (2) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 30mm |
| Mounting Hole Spacing | 20-22mm |
| Material | Zinc alloy |
| IP Rating | IP67 |
| Operating Temperature | -30 to 80 deg C |
| Connection | M20 x 1.5 entry with 1/2in NPT adapter |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E57648 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |