061019-00 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Stego flat heater, 100W heating capacity, PTC resistor heating element, 120 VAC operating voltage, 50/60 Hz, M6 screw mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/061019-00

Technical Specifications

Brand	Stego
Item	Flat heater
IP Rating	IP20
Heating Capacity	100W
Heating Element	PTC resistor
Operating Voltage	120 VAC
Hertz	50/60 Hz
Connection	3.3ft silicone cable with (3) 18 AWG conductors
Mounting	M6 screw

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/061019-00.pdf
See store item page for other formats.