# 1418T20 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Hammond enclosure, NEMA 12/13, 60 x 36 x 20in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/1418T20

## Technical Specifications

| | |
|---|---|
| **Brand** | Hammond |
| **Item** | Enclosure |
| **Subpanel** | Subpanel included |
| **Slope Top** | No |
| **3-Piece Assembly** | No |
| **Vented** | No |
| **NEMA Rating** | 12/13 |
| **IP Rating** | IP54 |
| **Nominal Enclosure Dimensions** | 60 x 36 x 20in (HxWxD) |
| **Enclosure Height** | 60.00in |
| **Enclosure Width** | 36.00in |
| **Enclosure Depth** | 21.20in |
| **Mounting** | Wall |
| **Integral Mounting Feet** | Yes |
| **Integral Mounting Flange** | No |

| | |
|---|---|
| **Dual Access** | No |
| **Knockouts** | No |
| **Bottom Gland Plate** | No |
| **Material** | Carbon steel |
| **Color** | ANSI 61 gray |
| **Finish** | Powder coat |
| **Cover Type** | Single-door |
| **Hinge Type** | Continuous hinge |
| **Number of Hinges Per Door** | 1 |
| **Latch Type** | Stainless steel clamps |
| **Number Of Latches** | 3 |
| **Padlock Attachment Type** | Padlock hasp and staple |
| **Shelf** | No |
| **Padlockable** | Yes |
| **Keylocking** | No |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E65324 |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CE** | View CE declarations |
| **CSA File #** | LR21001 |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/1418T20.pdf
See store item page for other formats.