1490G8 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Hammond pushbutton consolet, 8 holes, 30mm, NEMA 12/13, 7 x 11 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/1490G8

Technical Specifications

Brand	Hammond
Item	Pushbutton consolet
Number of Pushbutton Holes	8 holes
Pushbutton Hole Nominal Size	30mm
Slope Top	No
NEMA Rating	12/13
IP Rating	IP54
Nominal Enclosure Dimensions	7 x 11 x 7in (HxWxD)
Enclosure Height	6.78in
Enclosure Width	11.06in
Enclosure Depth	6.94in

Mounting	Desktop or pedestal
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Hinged screw cover
Hinge Type	Internal lift-off hinge
Number of Hinges Per Door	2
Additional Information	Purchase optional pedestal column separately

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document