# 70920FR Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Bryant industrial heavy duty single locking blade receptacle, 20A, 600 VAC, 1-phase, 2-pole, 3-wire, NEMA L9-20, nylon molded housing, black.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/70920FR

## Technical Specifications

| | |
|---|---|
| **Brand** | Bryant |
| **Item** | Receptacle |
| **Application** | Industrial heavy duty |
| **Receptacle Type** | Single |
| **Blade Type** | Locking |
| **With Cap** | No |
| **Self-grounding** | No |
| **Amperage Rating** | 20A |
| **Voltage Rating** | 600 VAC |
| **Number of Phases** | 1 |
| **Number of Poles** | 2 |
| **Number of Wires** | 3 |
| **Wire Size** | 14-8 AWG solid or stranded |
| **Copper Wire Only** | Yes |
| **Configuration** | NEMA L9-20 |
| **Housing Material** | Nylon molded |
| **Color** | Black |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E2258 |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CE** | View CE declarations |
| **CSA File #** | 016215 |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |